
© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Rocker switch and rocker button insert 10 A 250 V~ 2-way switch/2-way momentary contact



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 with mounting claws	3139 00	1/10	26.76	01	4010337039136
 without mounting claws	3869 00	1/10	26.76	01	4010337064565

Features

- Rocker switch and button in which the left rocker is laid out as a switch and the right rocker is laid out as a push button.
- For switching and colour control of an LED orientation light.
- For controlling motion detectors manually.
- For activating dimmer auxiliary units.
- For controlling switched lighting.

Technical data

Installation depth:	32 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm²
Rated output - LEDi/CFLi:	100 W

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.