© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Danish socket outlet 16 A 250 V~ 107-2-D1, DK 1-1b with increased contact protection (Safety Plus) System 55



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	4422 01	1/5	20.63	01	4010337092308
 pure white glossy	4422 03	1/5	20.63	01	4010337092322
 pure white matt	4422 27	1/5	20.63	01	4010337092346
 anthracite	4422 28	1/5	21.83	11	4010337092353
 colour aluminium (lacquered)	4422 26	1/5	26.22	11	4010337092339
 black matt (lacquered)	4422 005	1/5	26.22	11	4010337092292
 grey matt (lacquered)	4422 015	1/5	26.22	11	4010337092315

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

- Earthed support ring.

Technical data

Installation depth:	29 mm
Connection cross section - for conductors from:	1.5 mm² to 2.5 mm²

Notes

- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
