© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

eNet Radio wall transmitter, 3-gang System 55, rockers with inscription space



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 clear / pure white glossy	5333 100	1	118.64	42	4010337116547

Features

- The eNet wireless transmitters send switching, dimming and blind motion commands to corresponding eNet wireless receivers.
- Simple expansion of existing switch combinations.
- Can be installed without surface-mounted housing or device box.
- The wireless wall transmitter can be attached to walls with screws or glued onto smooth or transparent surfaces with the mounting plate.
- Transmission of switching, dimming, blind adjustment, and scene commands.
- Switchover function, optimised for the control of momentary-contact actuators.
- Rocker can be set as channel or scene function.
- Two-colour LEDs on the right and left of the buttons for signalling.
- Battery-operated device.

Technical data

Ambient temperature:	-5 °C to +45 °C
Wireless frequency:	868.3 MHz
Range (free field):	approx. 100 m
Rated voltage:	DC 3 V
Battery	
- Type:	1 x CR 2450N
- UN no.:	3091

Notes

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.
- The wireless wall transmitter is supplied with a program-neutral start-up rocker. The suitable rocker set for the switch range must be ordered separately.
- The range may be reduced when using metal rocket sets and/or metal cover frames.

Scope of supply

- Batteries are included with delivery.
