© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

USB power supply insert PD, 1-gang, 65 wattts Type C



Specification	Order No.	Packing unit	PS	EAN
 white	2362 00	1		4010337125259
 black	2363 00	1		4010337125242

Features

- The USB power supply insert type C with Power Delivery facilitates rapid charging where the device to be connected also has Power Delivery technology.
- The connected device determines the appropriate charge voltage from the power supply options. 5, 9, 15 or 20 volts are possible with 3.25 amps. That gives a charging capacity of up to 65 watts (20 V x 3.25 A).
- Adjustable charging is possible thanks to Power Delivery technology.
- Charging station for mobile device batteries with USB C connection.
- 1 USB type-C pin jack.
- Short-circuit-proof and overload-protected.
- Connection in accordance with USB Power Delivery Specification Revision 3.2.

Technical data

Rated voltage:	AC 220–240 V, 50/60 Hz
Output voltage:	DC 5 to 20 V
Output current:	max. 3.25 A
Power capacity:	15 to 65 W
Standby:	< 0.09 W
Protection class:	II
Connection cross section:	max. 2.5 mm^2
Installation depth:	32 mm
Ambient temperature:	0°C to +35°C

Illustrations are similar and may deviate from originals.