© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Blind rocker switch insert 10 A 250 V~**



| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
|  with mounting claws | 3159 00 | 1/10/100 | | 4010337039211 |
|  without mounting claws | 3879 00 | 1/10 | | 4010337064428 |

**Features**

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- LED lighting elements can be inserted from the front as standard.
- With block to prevent both sides from being switched on.
- Locked both electrically and mechanically.

**Technical data**

Installation depth
- 3159 00: 32 mm
- 3879 00: 23 mm

Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Notes**

- Suitable for use as an auxiliary unit for the blind controller insert with auxiliary input.

---

Illustrations are similar and may deviate from originals.