© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Power supply DC 12 V 2 A**




| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
|  DRA | 5319 00 | 1 | | 4010337774037 |

**Features**

- Power supply DC 12 V for the eNet server, eNet wireless receiver module and external camera.

**Technical data**

| | |
|---|---|
| Rated voltage | |
| - Primary: | AC 100 to 240 V, 50/60 Hz |
| - Secondary: | DC 12 to 14 V |
| Rated current | |
| - Secondary: | 2 A |
| Leakage current: | max. 250 µA |
| Ambient temperature: | -10 °C to +50 °C |

**Dimensions**

| | |
|---|---|
| Modular width (MW): | 2 |

Illustrations are similar and may deviate from originals.