









eNet wireless operating top unit



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  • cream white glossy | 5495 01 | 1/5 | 102.99 | 42 | 4010337104537 |
|  • pure white glossy | 5495 03 | 1/5 | 102.99 | 42 | 4010337104513 |
|  • pure white matt | 5495 27 | 1/5 | 102.99 | 42 | 4010337104490 |
|  • anthracite | 5495 28 | 1/5 | 105.63 | 42 | 4010337104483 |
|  • colour aluminium | 5495 26 | 1/5 | 108.79 | 42 | 4010337104476 |
|  • black matt | 5495 005 | 1/5 | 108.79 | 42 | 4010337104452 |
|  • grey matt | 5495 015 | 1/5 | 108.79 | 42 | 4010337104445 |
|  • stainless steel | 5495 600 | 1/5 | 115.68 | 42 | 4010337104469 |

Merkmale

- Operation on switching, dimming or blind insert or 3-wire auxiliary insert from System 3000.
- Manual, wireless and time-controlled operation of e.g. blinds, shutters, awnings, lighting or fans.
- Transmitter for wireless transmission of switching, dimming and blind commands.
- Adjustable night mode. Status LED and function LED are not lit up continuously.
- Status feedback to wireless transmitter.
- Status display with LED.
- Evaluation of auxiliary inputs.

Functions in combination with blind insert:

- Positioning of hangings via scene call-up.
- Position for sun protection and twilight.
- Runtime and ventilation position of the curtain can be saved.

Functions in combination with light insert:

- Scene operation possible.
- Switch-on brightness can be permanently stored when combined with dimming insert.

Functions in combination with 3-wire auxiliary unit:

- Power-supplied eNet transmitter.
- Lighting control.
- Shading control.

Adjustable with eNet server version 2.3 and higher (depending on the insert):

- Fully encrypted wireless transmission (AES-CCM).
- Deactivate auxiliary unit evaluation.
- Operation locks.
- Reversal time adjustable for blinds, shutters and awnings.
- Direction of travel can be inverted.
- Position for sun protection, twilight, lock-out protection and wind alarm.
- Maximum brightness, minimum brightness and dimming speed adjustable.
- Function of the status LED can be set as status LED/actuation display.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Device software update.

Technische Daten

| | |
|----------------------|--------------------|
| Ambient temperature: | -5 °C to +45 °C |
| Wireless frequency: | 868.0 to 868.6 MHz |
| Range (free field): | approx. 100 m |

Hinweise

- Using a metal cover frame can lead to impairments to the range
 - Radio approval is valid for EU and EFTA countries.
-