








## System 106 intercom module



Spezifikation	Bestell-Nr.	VE	PS	EAN
 stainless steel	5563 920	1		4010337022428
 aluminium	5563 926	-	-	4010337022411
 aluminium (anodised)	5563 916	1		4010337137948
 traffic white (laquered)	5563 902	1		4010337022404
 stainless steel V4A	5563 914	1		4010337091950
 bronze	5563 921	1		4010337100850
 black matt (lacquered)	5563 925	1		4010337100690

The Gira System 106 is an installation system made of metal in a puristic and elegant frameless design, based on basic measurements of 106.5 × 106.5 mm. With the modular door intercom in Gira System 106, hospitality begins even before you reach the front door. All the functions are presented in a harmonious overall appearance, from the call button module, intercom module, and camera module, up to the info and blank module. In the dark, backlit call buttons with inscription space ensure good legibility and an attractive appearance. Individually adaptable modular system The System 106 can be used in family homes or apartment buildings, as well as in office buildings, industrial properties, and hotels. The modular design enables the system's size, design, and functionality to be individually adapted to the respective requirements. Expansions and changes are possible at any time by easily exchanging the modules. With this system, it is also possible to exchange the fronts only. This means that the appearance of the system can be changed from e.g. traffic white to a stainless steel surface at a later stage, without having to exchange the electronic units. High-quality materials The modules are frameless with design fronts made of

genuine materials, available in two brushed stainless steel versions (V2A and V4A), anodised aluminium C-0, and a metal alloy lacquered in traffic white (RAL 9016): all robust materials which ensure durability. The camera and DIN 18040 display module feature a black glass cover. Easy and phased installationThe system can be installed in phases, in parallel to the progress of building work. In this way, it is possible to initially install only the lower part of a surface-mounted housing during construction of the shell; cables and modules can then be added when they are needed. Individual inscription optionsCall button modules and info modules can be labelled individually via the Gira inscription service.

---

## Merkmale

- The speakerphone function enables communication between indoors and outdoors.
  - A high-quality microphone and weather-resistant loudspeaker ensure clear communication.
  - Power supply via 2-wire bus. Additional connector for AS (e.g. required for three or more camera modules).
  - All other System 106 modules (except door station module) are supplied with power via the intercom module.
- 

## Technische Daten

### Power supply

- System: Flat ribbon cable, 10-pole
- 2-wire bus: via control device or via AS (DC 24 V 300 mA)

### Power consumption

- Maximum: 1 W
- Standby mode: 200 mW

### Connections

- 2-wire bus: 1 x plug terminal
- AS: 1 x plug terminal
- System: 2 x connector strip
- Video (analogue): 1 x connector strip

Ambient temperature: -25 °C to +70 °C

Protection class: IP54

---