


Basic Q smoke alarm device



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSSt.	PS	EAN
	1149 02	1	32.77	03	4010337016694

Increased quality criteria and technical advancements in smoke alarm devices are indicated on the market with the new Q test mark. The new Q-Label is an autonomous, manufacturer-independent quality mark for high-quality smoke alarm devices which undergo special testing for long-term use. The latest generation of Gira smoke alarm devices fulfil the criteria of the new Q-Label quality mark. The smoke alarm devices operate based on the photoelectric scattered light principle without radioactive particles. The smoke alarm devices detect smoke accumulation early and emit a warning signal before the concentration of smoke can become hazardous to people. Alerting occurs via a loud pulsing alarm tone and a flashing LED.

Merkmale

- Only for use in private residential units or residential-like areas in accordance with DIN 14676.

Q-Label

- Tested durability and reduction of false alarms.
- Increased stability, e.g. against external factors.
- Permanently installed battery with a service life of up to 10 years.
- designAccording to DIN EN 14604.
- KRIWAN approval.
- Integrated function button for function test.
- Fault indication.
- Weak battery indication.

Technische Daten

Ambient temperature:	-5 °C to +55 °C
Installation height:	Max. 6 m
Protection class:	IP30
Area of application:	DIN 14676
Standards:	DIN 14604

GIRA Parts list

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

design:	A
Power supply:	Via smoke alarm device battery
Batteries	
- Type:	3 x CR123A
- UN no.:	3091
Dimensions	
- Housing:	Ø 125,0 H 38,5 mm
Acoustic signal:	Alarm: at least 85 dB (A)
Optical signal:	Ring indicator (red LED)
