


Audio control device



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 DRA	1287 00	1	200.25	18	4010337287001

Merkmale

- Control device to supply power to the audio components of the Gira door communication bus.
- Power supply of the reverse-polarity protected and short-circuit-proof 2-wire bus.
- Self-resetting electronic short-circuit and overload recognition of the operating voltage and the bus connection.
- Buttons for system and door opener programming.
- LED status indicators for operation, overload, system programming, and door opener programming.
- Output AC 12 V for power supply of a standard door opener.
- Relay output for switching a door opener with its own power supply.
- Door opener time progressively adjustable from 1 to 10 s.

Technische Daten

Rated voltage	
- Primary:	AC 230 V, 50 Hz
- Secondary:	SELV 26 DC V \pm 2 V
Secondary rated current	
- Continuous load:	160 mA
- Peak load:	550 mA (max. 5 s)
- Overload deactivation:	from 350 mA
Connection cross section:	0.6 mm to 2.5 mm ²
Door opener output:	AC 12 V, max. 1.6 A / switch-on duration 25%
Relay output:	AC/DC 30 V, 2 A
Total cable length:	Max. 700 m
Cable length from control device to most distant device	
- for cable \varnothing 0.8 mm:	Max. 300 m
- for cable \varnothing 0.6 mm:	Max. 170 m
Ambient temperature:	-5 °C to +45 °C

Hinweise

- The audio control device is intended to be installed in the sub-distribution. If this is not possible, use a standard surface-mounted distributor.
- This component enables door communication systems with up to 70 devices to be set up (e.g. 1 x built-in speaker, 5 x add-on modules for built-in speakers, 68 x surface-mounted home stations).

Abmessungen

Teilungseinheiten (TE): 6
