


DCS switching actuator



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSSt.	PS	EAN
 DRA	1289 00	1	140.17	18	4010337289005

Merkmale

- Switching actuator for switching light, controlling a door opener on back/side doors or other functions using the Gira door communication bus.
- Actuation of a zero-voltage switching contact 230 V / 10 A via the 2-wire bus.
- The switching actuator can be actuated by: the "Door" and "Light" buttons on the home station, the call button on the door station, the call button on the home station.
- The switching actuator can be used in five different operating modes: switching, timer/sec., timer/min., pulse, and door opener.
- Impulse function for controlling existing automatic staircase mechanisms.
- Binary input for switching functions via a connected mechanical push button.
- Switching time can be adjusted progressively from 1 to 10 s or 1 to 10 min., depending on the function set.

Technische Daten

Power supply:	via the 2-wire bus
Zero-voltage relay contact	
- either:	2 A at DC 30 V
Number of call buttons that can be taught in:	max. 16
Ambient temperature:	-5 °C to +45 °C

Hinweise

- The switching actuator is intended to be installed in the sub-distribution. If this is not possible, use a standard surface-mounted distributor.
- This component enables door communication systems with more than 30 devices to be set up.

Abmessungen

Teilungseinheiten (TE): 2
