© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Room climate sensor HVAC Standard for KNX System 55**




| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  cream white glossy | 2006 01 | 1/5 | 134.10 | 06 | 4010337130598 |
|  pure white glossy | 2006 03 | 1/5 | 134.10 | 06 | 4010337130604 |
|  pure white matt | 2006 27 | 1/5 | 134.10 | 06 | 4010337130611 |
|  anthracite | 2006 28 | 1/5 | 136.78 | 06 | 4010337130628 |
|  colour aluminium (lacquered) | 2006 26 | 1/5 | 139.46 | 06 | 4010337130635 |
|  black matt (lacquered) | 2006 005 | 1/5 | 139.46 | 06 | 4010337130642 |
|  grey matt (lacquered) | 2006 015 | 1/5 | 139.46 | 06 | 4010337130680 |
|  stainless steel (lacquered) | 2006 600 | 1/5 | 146.17 | 06 | 4010337130697 |

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Features**

- Room climate sensor HVAC with integrated bus coupler.
- Segment-based display: Display of the operating mode (comfort, lowering temperature, night-time lowering, eco), window status, operation lock, fan level, heating/cooling mode.
- Display brightness can be configured incl. day/night mode.
- Integrated temperature sensor.

Operating functions

- Setpoint adjustment.
- Operating mode change.
- Operation lock can be set manually, automatically after a set time or via an object.
- Switch on/off function.
- Fan level.
- Heartbeat function: Check whether the application is error-free.

Fancoil control with integrated controller

- Display/adjustment of target/actual temperature, operating mode, heating/cooling status.
- Fan speed can be adjusted (on, off, auto, stepped operation).
- Feedback on fan level and operating mode.
- Objects for manual control.

Split-unit control

- Set target temperature.
- Operating modes: automatic, heating, cooling, ventilation, eco, boost.
- Set fan speed, switch-off possible.

---

**Technical data**

| | |
|---|---|
| KNX medium: | TP256 |
| KNX current consumption: | 8 to 14 mA |
| KNX connection: | Connection and junction terminal |
| Protection class: | III |
| Installation depth: | 19 mm |
| Ambient temperature: | -5 °C to +45 °C |
| Relative humidity: | 5 to 95% (no condensation) |

---

**Notes**

- KNX Data Secure compatible.
- Can be updated.
- Configuration and start-up of the device from ETS 5 version 5.7.7 or higher or ETS 6 version 6.3 or higher (recommended).

---

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Scope of supply**

- Connection and junction terminal for KNX included with delivery.

---