

Room climate sensor HVAC Standard for KNX System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2006 01	1/5	134.10	06	4010337130598
 pure white glossy	2006 03	1/5	134.10	06	4010337130604
 pure white matt	2006 27	1/5	134.10	06	4010337130611
 anthracite	2006 28	1/5	136.78	06	4010337130628
 colour aluminium	2006 26	1/5	139.46	06	4010337130635
 black matt	2006 005	1/5	139.46	06	4010337130642
 grey matt	2006 015	1/5	139.46	06	4010337130680
 stainless steel (lacquered)	2006 600	1/5	146.17	06	4010337130697

Merkmale

- Room climate sensor HVAC with integrated bus coupler.
- Segment-based display: Display of the operating mode (comfort, lowering temperature, night-time lowering, eco), window status, operation lock, fan level, heating/cooling mode.
- Display brightness can be configured incl. day/night mode.
- Integrated temperature sensor.

Operating functions

- Setpoint adjustment.
- Operating mode change.
- Operation lock can be set manually, automatically after a set time or via an object.
- Switch on/off function.

Technische Daten

KNX medium:	TP256
KNX current consumption:	8 to 14 mA
KNX connection:	Connection and junction terminal
Protection class:	III
Installation depth:	19 mm
Ambient temperature:	-5 °C to +45 °C
Relative humidity:	5 to 95% (no condensation)

Hinweise

- KNX Data Secure compatible.
- Can be updated.
- Configuration and start-up of the device from ETS 5 version 5.7.7 or higher or ETS 6 version 6.3 or higher (recommended).

Lieferumfang

- Connection and junction terminal for KNX included with delivery.
-