


Room climate sensor HVAC Standard for KNX System 70



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSSt.	PS	EAN
 pure white glossy	2006 70	1/5	134.10	06	4010337130703
 pure white matt (lacquered)	2006 72	1/5	134.10	06	4010337130710
 anthracite (lacquered)	2006 73	1/5	136.78	06	4010337130727
 black matt (lacquered)	2006 74	1/5	139.46	06	4010337130734
 grey matt (lacquered)	2006 76	1/5	139.46	06	4010337130741

Merkmale

- Room climate sensor HVAC with integrated bus coupler.
- Segment-based display: Display of the operating mode (comfort, lowering temperature, night-time lowering, eco), window status, operation lock, fan level, heating/cooling mode.
- Display brightness can be configured incl. day/night mode.
- Integrated temperature sensor.

Operating functions

- Setpoint adjustment.
- Operating mode change.
- Operation lock can be set manually, automatically after a set time or via an object.
- Switch on/off function.
- Fan level.
- Heartbeat function: Check whether the application is error-free.

Fancoil control with integrated controller

- Display/adjustment of target/actual temperature, operating mode, heating/cooling status.
- Fan speed can be adjusted (on, off, auto, stepped operation).
- Feedback on fan level and operating mode.
- Objects for manual control.

Split-unit control

- Set target temperature.
- Operating modes: automatic, heating, cooling, ventilation, eco, boost.
- Set fan speed, switch-off possible.

Technische Daten

KNX medium:	TP256
KNX current consumption:	8 to 14 mA
KNX connection:	Connection and junction terminal
Protection class:	III
Installation depth:	19 mm
Ambient temperature:	-5 °C to +45 °C
Relative humidity:	5 to 95% (no condensation)

Hinweise

- KNX Data Secure compatible.
- Can be updated.
- Configuration and start-up of the device from ETS 5 version 5.7.7 or higher or ETS 6 version 6.3 or higher (recommended).

Lieferumfang

- KNX connection and junction terminal included in the scope of delivery.
-