









## Room climate sensor HVAC Komfort for KNX System 55



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2007 01	1/5	179.10	06	4010337130758
 pure white glossy	2007 03	1/5	179.10	06	4010337130765
 pure white matt	2007 27	1/5	179.10	06	4010337130772
 anthracite	2007 28	1/5	182.68	06	4010337130789
 colour aluminium	2007 26	1/5	186.26	06	4010337130796
 black matt	2007 005	1/5	186.26	06	4010337130802
 grey matt	2007 015	1/5	186.26	06	4010337130819
 stainless steel (lacquered)	2007 600	1/5	195.22	06	4010337130826

## Merkmale

- Room climate sensor with integrates bus coupler.
- Room temperature auxiliary unit for a heating actuator with controller.
- Segment-based display: Display of the operating mode (comfort, lowering temperature, night-time lowering, eco), window status, operation lock, fan level, heating/cooling mode, humidity and air quality status as a configurable traffic light indicator.
- Display brightness can be configured incl. day/night mode.
- Integrated temperature and humidity sensor.
- Connection of an external temperature sensor.
- Dew point determination and alarm function.

### Operating functions

- Setpoint adjustment.
- Operating mode change.
- Operation lock can be set automatically after a set time or via an object.
- Switch on/off function.
- Fan level.
- Heartbeat function: Check whether the application is running without errors.

### Fancoil control with integrated controller

- Display/adjustment of target/actual temperature, operating mode, heating/cooling status.
- Fan speed can be adjusted (on, off, auto, stepped operation).
- Feedback on fan level and operating mode.
- Objects for manual control.

### Split-unit control

- Set target temperature.
- Operating modes: automatic, heating, cooling, ventilation, eco, boost.
- Set fan speed, switch-off possible.

### Integrated button interface, 4-gang

- 4 zero-voltage inputs for buttons, switches, door/window status, leakage/condensation sensor, pulse counter, temperature sensor, output.
- Scene auxiliary units and value transmitter functions (temperature, brightness, RGBW colour values).
- Different telegrams with short/long button press.
- Short-circuit-proof, overload-protected and reverse-polarity-protected outputs.

### Logic functions

- 8 separate logic functions (AND, OR, XOR, 1-bit to 1-byte, blocking element, comparator, limit switch).
- Dedicated KNX communication objects, processing of external KNX telegrams.

---

## Technische Daten

KNX medium:	TP256
KNX current consumption:	8 to 14 mA
KNX connection:	Connection and junction terminal
Number of inputs:	4
Output voltage:	DC 5 V SELV
Output current:	Max. 3.2 mA
LED current:	2.2 mA per output
Length cable set:	25 cm, can be extended to max. 30 m

Protection class:	III
Installation depth:	19 mm
Ambient temperature:	-5 °C to +45 °C
Relative humidity:	5 to 95% (no condensation)

---

## Hinweise

- KNX Data Secure compatible.
  - Firmware can be updated using the Gira ETS Service App (additional software).
  - Configuration and start-up of the device from ETS 5 version 5.7.7 or higher or ETS 6 version 6.3 or higher (recommended).
- 

## Lieferumfang

- KNX connection and junction terminal included in the scope of delivery.
  - 5-wire cable set
-