


## IR gateway HVAC for KNX



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
	2029 00	1	260.10	06	4010337132714

### Merkmale

- KNX gateway for integrating air conditioning units into a KNX system.
- Configuration via ETS.
- KNX Data Secure certified.
- Room temperature measurement: Measurement of the room temperature by internal sensors.
- Room humidity measurement: Measurement of the room humidity by internal sensors.
- Scene function: Storage of up to 10 scenes.
- 2 binary inputs, e.g. for connecting window contacts.
- Power supply via KNX bus, so no additional power supply is required.
- LED display for programming status.
- 1 USB type-C pin jack.
- Compatible with all common split-unit air conditioning products from various manufacturers.
- Bidirectional IR interface.
- Updatable IR code database.

### Technische Daten

KNX operating voltage:	DC 29 V
KNX current consumption:	17 mA
KNX connection:	Connection and junction terminal
Ambient temperature:	0°C to +60°C
Relative humidity:	5 to 95% (no condensation)
Mounting type:	Wall mounting

## Hinweise

- Installation indoors only. Avoid direct sunlight, contact with water, high humidity and dust.

---