© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Heating actuator Basic, 6-gang for KNX



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 DRA	2114 00	1	163.49	26	4010337018414

Features

- Heating actuator for switching thermal servos for heating systems or cooling ceilings.
- Control using 1-bit or 1-byte corrected variable telegrams.
- For 1-byte correcting variables, the outputs are controlled by pulse width modulation (PWM).
- Valve drives with the characteristic "de-energised open" or "de-energised closed" can be controlled.
- Servos with 24 V or 230 V rated voltage can be actuated.
- Overload protected, short-circuit-proof.
- Standard protection.
- Feedback via bus e.g. in the event of overload and short circuit.
- Switching the heating circuit pump (standard functions).
- Passive group feedback of the closed valve drives.

Technical data

KNX medium:	TP256
Outputs:	6
Contact type:	Triac
Power loss:	max. 1 W
Switching voltage:	AC 24/230 V, 50/60 Hz
Switching current:	5 to 160 mA
Switch-on current:	max. 1.5 A (2 s)
Number of drives per output - AC 230 V drives: - AC 24 V drives:	 4 2
Connection cross section:	Max. 4 mm²

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Notes

- Valves with the same operating voltage must be connected at all outputs.
- VDE approval in accordance with EN 60669-1, EN 60669-2-1.
- Installation on DIN top-hat rail.

Dimensions

Modular width (MW):	4
