

Gira Keyless In Keypad System 55



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 cream white glossy	2605 01	1	280.46	10	4010337051343
 pure white glossy	2605 03	1	280.46	10	4010337051350
 pure white matt	2605 27	1	280.46	10	4010337051374
 anthracite	2605 28	1	284.99	10	4010337051381
 colour aluminium (lacquered)	2605 26	1	290.79	10	4010337051367
 black matt (lacquered)	2605 005	1	290.79	10	4010337037125
 grey matt (lacquered)	2605 015	1	290.79	10	4010337084662

Features

- Keypad as an access control system with a capacitive and therefore wear-free button field.
- No recognisable wear on frequently used number combinations.
- Stand-alone device or in combination with the Gira door communication system as a door call system for buildings with several residential units.
- Special button "C": Deleting an incorrect entry.
- Special button "Key": Direct door opening when the correct code has been entered.
- Special button "Bell": Specific selection of home stations in large facilities.
- Special button "F": Switching functions with switching actuators from the Gira door communication system.
- Homogeneous blue LED lighting of the numbers and special characters at night.
- Master PIN number provided on included sealed safety card if Administrator PIN number is lost.

The keypad can manage up to 255 codes.

Illustrations are similar and may deviate from originals.

Prices valid for United Kingdom with prices valid 01/26.

- Audible feedback when buttons are touched.

- 3-colour LED status display when programming and during operation.

Inputs and outputs

- Connector strip connection cable for Gira door communication system.

Technical data

Power supply

- Additional power supply: DC 24 V $\pm 5\%$
- from door communication system: DC 26 V ± 2 V

Relay

- Quantity: 2
- Contact: 1 zero-voltage 2-way momentary contact
- Load capacity: AC/DC 24 V / 1.6 A

Connections

- Connection cable for door communication: 1 x connector strip
- Relay: 3 screw terminals each
- Additional power supply: 2 x screw terminal

Resistance to EMD: up to 16 kV

Installation depth: 35 mm

Ambient temperature: -20 °C to +70 °C

Notes

- Keyless In devices can be connected to the Gira HomeServer using the DCS-IP gateway. This enables intelligent links. In this way, e.g. temporary or one-time access authorisation can be easily granted. All data including access authorisations can be managed centrally and flexibly using the Gira HomeServer.
- Integration into Profile 55 possible.
- The Gira AppShop is the marketplace for interesting solutions and applications in intelligent building technology. There are now more than 200 apps available, including application descriptions, plug-ins, function templates, logic nodes and sample projects. Discover applications for the Gira Keyless In keypad now. www.appshop.gira.de/en.