© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Gira Keyless In Keypad TX_44



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 pure white	2605 66	1	290.79	10	4010337051428
 anthracite (lacquered)	2605 67	1	301.17	10	4010337051435
 colour aluminium (lacquered)	2605 65	1	301.17	10	4010337051411

Features

- Keypad as an access control system with a capacitive and therefore wear-free button field.
- No recognisable wear on frequently used number combinations.
- Stand-alone device or in combination with the Gira door communication system as a door call system for buildings with several residential units.
- Special button "C": Deleting an incorrect entry.
- Special button "Key": Direct door opening when the correct code has been entered.
- Special button "Bell": Specific selection of home stations in large facilities.
- Special button "F": Switching functions with switching actuators from the Gira door communication system.
- Homogeneous blue LED lighting of the numbers and special characters at night.
- Master PIN number provided on included sealed safety card if Administrator PIN number is lost.
- The keypad can manage up to 255 codes.
- Up to 32-digit codes are possible.
- Audible feedback when buttons are touched.
- 3-colour LED status display when programming and during operation.
- Warning tone in case of unauthorised removal of the keypad top unit for tamper detection. Tampering circuit with switching actuator in the Gira door communication system.
- The two integrated 2-way momentary contact relays can be assigned two different codes, e.g. code 1: open door, code 2: switching outside light.

Inputs and outputs

- Connector strip connection cable for Gira door communication system.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Technical data

Power supply	
- Additional power supply:	DC 24 V ±5%
- from the door communicationsystem:	DC 26 V ± 2 V
Relay	
- Quantity:	2
- Contact:	1 zero-voltage 2-way momentary contact
- Load capacity:	AC/DC 24 V / 1.6 A
Connections	
- Connection cable for door communication:	1 x connector strip
- Relay:	3 screw terminals each
- Additional power supply:	2 x screw terminal
Resistance to EMD:	up to 16 kV
Installation depth:	35 mm
Ambient temperature:	-20 °C to +70 °C

Notes

- Keyless In devices can be connected to the Gira HomeServer using the DCS-IP gateway. This enables intelligent links. In this way, e.g. temporary or one-time access authorisation can be easily granted. All data including access authorisations can be managed centrally and flexibly using the Gira HomeServer.
- The Gira AppShop is the marketplace for interesting solutions and applications in intelligent building technology. There are now more than 200 apps available, including application descriptions, plug-ins, function templates, logic nodes and sample projects. Discover applications for the Gira Keyless In keypad now.www.appshop.gira.de/en.
