








RCD-protected socket outlet 30 mA with increased contact protection (Safety Plus)



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
 cream white glossy	2677 01	1	164.21	03	4010337011941
 pure white glossy	2677 03	1	164.21	03	4010337011958
 pure white matt	2677 27	1	164.21	03	4010337011965
 anthracite	2677 28	1	166.73	03	4010337011972
 colour aluminium	2677 26	1	168.26	03	4010337011989
 black matt	2677 005	1	168.26	03	4010337037071
 grey matt	2677 015	1	168.26	03	4010337085249

Merkmale

- The RCD-protected socket outlet is a built-in protective device with a voltage-independent residual current tripping in accordance with VDE 0664.
- This device works like an RCD switch.

Technische Daten

Rated voltage:	AC 230 V, 50/60 Hz
Rated current:	16 A
Rated residual current:	30 mA
Installation depth:	32 mm
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature:	-25 °C to +40 °C

Hinweise

- Mounting in a deep device box.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
 - Residual current devices (RCDs) in a unit with one socket outlet can also provide protection for an adjacent socket outlet (under a shared cover), DIN VDE 0100-530:2018-06.
-