








RCD-protected socket outlet 30 mA with increased contact protection (Safety Plus)



| Spezifikation | Bestell-Nr. | VE | GBP/Stück o. MWSt. | PS | EAN |
|---|-------------|----|--------------------|----|---------------|
|  cream white glossy | 2677 01 | 1 | 164.21 | 03 | 4010337011941 |
|  pure white glossy | 2677 03 | 1 | 164.21 | 03 | 4010337011958 |
|  pure white matt | 2677 27 | 1 | 164.21 | 03 | 4010337011965 |
|  anthracite | 2677 28 | 1 | 166.73 | 03 | 4010337011972 |
|  colour aluminium | 2677 26 | 1 | 168.26 | 03 | 4010337011989 |
|  black matt | 2677 005 | 1 | 168.26 | 03 | 4010337037071 |
|  grey matt | 2677 015 | 1 | 168.26 | 03 | 4010337085249 |

Merkmale

- The RCD-protected socket outlet is a built-in protective device with a voltage-independent residual current tripping in accordance with VDE 0664.
- This device works like an RCD switch.

Technische Daten

| | |
|--|--|
| Rated voltage: | AC 230 V, 50/60 Hz |
| Rated current: | 16 A |
| Rated residual current: | 30 mA |
| Installation depth: | 32 mm |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature: | -25 °C to +40 °C |

Hinweise

- Mounting in a deep device box.
 - Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
 - Residual current devices (RCDs) in a unit with one socket outlet can also provide protection for an adjacent socket outlet (under a shared cover), DIN VDE 0100-530:2018-06.
-