© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Bus coupler button WP SM, 1-gang with control window and two-point operation for KNX**



| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  grey | 5152 30 | 1 | 92.78 | 06 | 4010337500070 |

The bus coupler button is the interface between the KNX system and the user.

**Features**

Button function

- Switching, dimming, blind, value transmitter 1-byte, and scene auxiliary unit.
- Switching function: Command for pressing and releasing the buttons can be parameterised (ON, OFF, CHANGE, no reaction).
- Dimming function: Command for pressing the buttons can be parameterised (Brighter-ON, Darker-OFF, Brighter or Darker-CHANGE, Brighter-CHANGE, Darker-CHANGE, no reaction).
- Blind function: Command for pressing the buttons can be parameterised (UP, DOWN, no reaction).
- Value transmitter 1-byte function: Mode of operation can be configured.
- Scene auxiliary unit function: Mode of operation can be configured (with or without block function for pressing and holding a button).
- Two-point operation (upright rocker) allows both-sided (e.g. top / bottom) rocker operation.
- Bus coupler button in the water-protected surface-mounted system (IP44).
- Functions of the status LED: Red LED can either be used as an orientation light, actuation display, or status display.
- The rocker or button function operating concepts can be set.

Rocker function

- Switching, dimming, and blinds
- Command for top and bottom rocker actuation can be parameterised (ON, OFF, CHANGE, no reaction).
- Command for top and bottom rocker actuation can be parameterised (Brighter-ON, Darker-OFF, Bright/darker-CHANGE, Brighter-CHANGE, Darker-CHANGE, no reaction).
- Command for rocker actuation can be parameterised (rocker top: UP / rocker bottom: DOWN, rocker top: DOWN / rocker bottom: UP).

**Technical data**

| | |
|---|---|
| KNX medium: | TP256 |
| KNX connection: | Connection and junction terminal |

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



| | |
|---|---|
| Protection class: | IP44 |
| Ambient temperature: | -25 °C to +55 °C |
| Relative humidity: | 5 to 93 % (without condensation) |

---

**Scope of supply**

- Connection and junction terminal for KNX included with delivery.

---