


Bus coupler button WP SM, 2-gang with single-point operation for KNX



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSSt.	PS	EAN
 grey	5161 30	1	90.38	06	4010337500087

The bus coupler button is the interface between the KNX system and the user.

Merkmale

Button function

- Switching, dimming, blind, value transmitter 1-byte, and scene auxiliary unit.
- Switching function: Command for pressing and releasing the buttons can be parameterised (ON, OFF, CHANGE, no reaction).
- Dimming function: Command for pressing the buttons can be parameterised (Brighter-ON, Darker-OFF, Brighter or Darker-CHANGE, Brighter-CHANGE, Darker-CHANGE, no reaction).
- Blind function: Command for pressing the buttons can be parameterised (UP, DOWN, no reaction).
- Value transmitter 1-byte function: Mode of operation can be configured.
- Scene auxiliary unit function: Mode of operation can be configured (with or without block function for pressing and holding a button).
- Single-point operation (rocker at an angle) only allows one-sided (bottom) rocker operation.
- Bus coupler button in the water-protected surface-mounted system (IP44).

Technische Daten

KNX medium:	TP256
KNX connection:	Connection and junction terminal
Protection class:	IP44
Ambient temperature:	-25 °C to +55 °C
Relative humidity:	5 to 93 % (without condensation)

Lieferumfang

- Connection and junction terminal for KNX included with delivery.
