© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**RF wall transmitter, 2-gang, for KNX**



| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
| cream white glossy | 5178 01 | 1 | 121.90 | 06 | 4010337123026 |
| pure white glossy | 5178 03 | 1 | 121.90 | 06 | 4010337123033 |
| pure white matt | 5178 27 | 1 | 121.90 | 06 | 4010337123040 |
| anthracite | 5178 28 | 1 | 123.81 | 06 | 4010337123064 |
| colour aluminium (lacquered) | 5178 26 | 1 | 125.71 | 06 | 4010337123057 |
| black matt (lacquered) | 5178 005 | 1 | 125.71 | 06 | 4010337123088 |
| grey matt (lacquered) | 5178 015 | 1 | 125.71 | 06 | 4010337123071 |

**Features**

- The wall transmitter can be mounted on walls with screws or adhered to smooth or transparent surfaces with a mounting plate.
- Project planning, commissioning and parameter setting are performed using ETS (version 5 or later).
- Integrated USB Micro-B interface for local programming and can be used as a KNX RF interface.
- Battery-operated device.
- Device supports KNX Secure.

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



"Switching" function

- Command for pressing and releasing can be parameterised (ON, OFF, CHANGE, no reaction).
- Command with short or long keystroke.

"Dimming" function

- Command when the button is pressed can be set in the parameters (brighter-ON, darker-OFF, brighter/darker-CHANGE).

"Blind" function

- Command when the button is pressed can be set in the parameters (UP, DOWN, CHANGE).

“Value transmitter” function

- 1-byte, 2-byte, 3-byte, 14-byte ASCII.

“Colour” function

- RGB/RGBW colour control, toggling of 8 colour values.

“Scene auxiliary unit” function

- Scene retrieval and saving possible, toggling of 8 scenes.

“Individual” function

- Various function combinations when the button is pressed or released.
- With scene auxiliary unit: Memory function possible.

---

**Technical data**

| | |
|---|---|
| KNX medium: | RF1.R |
| Start-up mode: | S mode |
| Rated voltage: | DC 3 V |
| Batteries: | 1 x CR 2032 |
| Ambient temperature: | -5 °C to +45 °C |
| Wireless frequency: | 868.3 MHz |
| Transmission power: | max. 20 mW |
| Range (free field): | approx. 100 m |

---

**Notes**

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
- A loss of range can occur when using metallic cover frames.
- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.

---

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Scope of supply**

- Batteries are included with delivery.
- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.

---