






## System 3000 room temperature controller Display System 70



| Spezifikation   | Bestell-Nr. | VE  | GBP/Stück o. MWSt. | PS | EAN           |
|---|-------------|-----|--------------------|----|---------------|
|  pure white glossy             | 5393 70     | 1/5 | 102.10             | 02 | 4010337118664 |
|  pure white matt (lacquered) | 5393 72     | 1/5 | 107.76             | 02 | 4010337118671 |
|  anthracite (lacquered)      | 5393 73     | 1/5 | 107.76             | 02 | 4010337118640 |
|  black matt (lacquered)      | 5393 74     | 1/5 | 107.76             | 02 | 4010337118688 |
|  grey matt (lacquered)       | 5393 76     | 1/5 | 107.76             | 02 | 4010337118657 |

### Merkmale

- Operation via capacitive sensor surface.
- Manual and time-controlled room temperature regulation.
- The current time can be stored as a switching time, quick programming.
- Automatic summer/winter time switchover, deactivatable.
- Timer with three memory areas. For each memory area comfort and lowering time for Mon-Fri and Sat+Sun.
- Setting of a comfort, reduction, cooling and frost protection temperature.
- Controller output: Pulse width modulation (PWM) or 2-point control.
- Heating optimisation (the temperature is reached at the set time).
- Adaptation to valves (normally open or normally closed).
- Activation of cooling mode via the insert.
- Supports internal and external temperature sensors.
- Temperature drop detection.
- Operation lock.
- Valve protection function.
- The display switches off after 2 minutes, permanent display of the current time is possible.
- The combination of the top unit 5394xx with 540700 is only possible for I05 (index) or higher.

## Technische Daten

|                      |                 |
|----------------------|-----------------|
| Accuracy per month:  | $\pm 10$ s      |
| Power reserve:       | approx. 4 h     |
| Ambient temperature: | -5 °C to +45 °C |

---