© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

eNet wireless dimming actuator, 1-gang Mini 20 – 250 W/VA



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
	5420 00	1/5	132.88	42	4010337774143

Features

- The eNet wireless dimming actuator enables the switching and dimming of various electrical loads.
- Switching and dimming light bulbs, HV halogen lamps, electronic transformers for halogen or LED lights, dimmable inductive transformers for halogen or LED lights, HV LED or compact fluorescent lamps.
- Switch-on function that preserves the life of the lamp.
- Switch-on and minimum brightness can be saved for each output.
- Scene operation.
- Status display with LED.
- Status feedback to eNet radio sensors.
- Short-circuit and excess-temperature protection.
- Automatic or manual setting of dimming process.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Power loss:	max. 1.5 W
Standby:	max. 0.5 W
Ambient temperature:	-25 °C to +70 °C
Connected load	
- Light bulbs:	20 to 250 W
- HV halogen lamps:	20 to 250 W
- Wound electronic transformer:	20 to 250 VA
- Wound transformer with NV-LED:	20 to 100 VA
- Tronic transformer:	20 to 250 W
- electronic transformer with NV-LED:	typically 20 to 100 W
- LED lights:	typically 3 to 70 W
- Compact fluorescent lamp:	typically 3 to 70 W
Connection cross section:	Max. 4 mm²
Wireless frequency:	868.0 to 868.6 MHz

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Range (free field):	approx. 100 m
Dimensions:	Ø 53,0 H 28,0 mm

Notes

- Mounting in device box, surface-mounted housing or in installation adapter.