

## eNet Radio blind actuator, 1-gang Mini



Spezifikation	Bestell-Nr.	VE	GBP/Stück o. MWSt.	PS	EAN
	5427 00	1/5	118.64	42	4010337774235

### Merkmale

- The eNet wireless blind actuator enables the control of electrically operated hangings such as blinds, shutters and awnings.
- Positioning of blinds and slats using scene call-up.
- Positions for sun protection and twilight can be saved.
- Status feedback to eNet radio transmitter.
- Curtain runtime can be saved.
- Slat adjustment time can be saved.

Can be set with eNet server:

- Adjustment time when changing directions.
- Direction of travel can be inverted (e.g. for roof windows).
- Position for solar protection, twilight, lock-out protection, and wind alarms.
- Behaviour after mains power failure.
- Repeater function.
- Localisation of the device.

### Technische Daten

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.5 W
Ambient temperature:	-25 °C to +70 °C
Connected load of motors:	1000 W
Connection cross section:	Max. 4 mm <sup>2</sup>
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m
Dimensions:	Ø 53,0 H 28,0 mm

## Hinweise

- Mounting in device box, surface-mounted housing or in installation adapter.

---