© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

eNet Radio switching/momentary-contact actuator, 8-gang / blind actuator, 4-gang



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 DRA	5435 00	1	332.22	42	4010337774280

Features

- The eNet wireless switching or momentary-contact or blind actuator receives telegrams for switching lighting or controlling electrically operated hangings from the eNet wireless receiver module or eNet server via a data line.
- Two outputs are each operated in the same mode (switching, pressing, blind or shutter).
- Switching of lighting or single-phase fan motors.
- Control of electrically operated hangings such as blinds, shutters and awnings.
- Operating modes: switching actuator, momentary-contact actuator can be set for a single output; a blind actuator, shutter actuator can be set for a pair of outputs.
- Status feedback to eNet radio transmitter.
- Scene operation.
- Operating mode buttons: Relay contact stays closed as long as telegrams are being received (max. 60 seconds).
- Positioning of blinds and slats using scene call-up.
- Positions for sun protection and twilight can be saved.
- Threshold value scenes for solar protection, twilight and wind alarms.
- Curtain runtime can be saved.
- Slat adjustment time can be saved.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.5 W
Ambient temperature:	-5 °C to +45 °C
Breaking capacity 230 V AC:	16 A/AC1
Connected load	
- Light bulbs:	2300 W
- HV halogen lamps:	2000 W
- Wound electronic transformer:	1000 VA
- Tronic transformer:	1500 W
- Fluorescent lamps, uncompensated:	920 VA
- LED lights:	typically 500 W
- Compact fluorescent lamp:	typically 500 W

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

- Motors:	1000 W
- Capacitive load:	690 VA (560 µF)
Connection cross section:	Max. 4 mm²
Length of the data line:	Max. 3 m

Notes

- An eNet wireless receiver module or an eNet server is required to operate this DIN rail adapter.

Dimensions

Modular width (MW):	4
