© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**eNet Radio energy sensor, 1-gang Mini**




| Specification | Order No. | Packing unit | GBP/piece without VAT | PS | EAN |
|---|---|---|---|---|---|
|  | 5471 00 | 1/5 | 90.17 | 42 | 4010337774365 |

**Features**

- The eNet radio energy sensors enable the radio transmission of voltage, electricity, and energy values to the eNet server.
- Logging electricity and voltage of the connected device.
- Calculation of effective output, reactive power, apparent power, and active electrical energy.
- Event- or time-controlled transmission of measurement value telegrams to the eNet server.
- Time synchronisation using the eNet server.

**Technical data**

| | |
|---|---|
| Rated voltage: | AC 230 V, 50/60 Hz |
| Ambient temperature: | -5 °C to +45 °C |
| Measurement range | |
| - Electricity: | 0 mA to 16 A |
| - Electrical power: | 0 to 3680 W |
| - Energy consumption: | 0 to 99999 kWh |
| Wireless frequency: | 868.3 MHz |
| Range (free field): | approx. 100 m |
| Rated load current: | 16 A |
| Connection cross section: | Max. 4 mm² |
| Dimensions: | Ø 53,0 H 23,0 mm |

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Notes**

- Mounting in device box, surface-mounted housing or in installation adapter.

---