© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

System 106 call-button module 3-gang



Specification	Order No.	Packing unit	GBP/piece without VAT	PS	EAN
 stainless steel	5533 920	1	232.88	20	4010337022565
 aluminium (anodised)	5533 916	1	202.61	20	4010337137979
 traffic white (laquered)	5533 902	1	202.61	20	4010337022534
 stainless steel V4A	5533 914	1	304.96	20	4010337091981
 Bronze (PVD)	5533 921	1	304.96	20	4010337100881
 black matt (lacquered)	5533 925	1	304.96	20	4010337100720

The Gira System 106 is an installation system made of metal in a puristic and elegant frameless design, based on basic measurements of 106.5 × 106.5 mm. With the modular door intercom in Gira System 106, hospitality begins even before you reach the front door. All the functions are presented in a harmonious overall appearance, from the call button module, intercom module, and camera module, up to the info and blank module. In the dark, backlit call buttons with inscription space ensure good legibility and an attractive appearance.Individually adaptable modular system The System 106 can be used in family homes or apartment buildings, as well as in office buildings, industrial properties, and hotels. The modular design enables the system s size, design, and functionality to be individually adapted to the respective requirements. Expansions and changes are possible at any time by easily exchanging the modules.With this system, it is also possible to exchange the fronts only. This means that the appearance of the system can be changed from e.g. traffic white to a stainless steel surface at a later stage, without having to exchange the electronic units.High-quality materialsThe modules are frameless with design fronts made of genuine materials, available in two brushed stainless steel versions (V2A and V4A), anodised aluminium C-0, and a metal alloy lacquered in traffic white (RAL 9016): all robust materials which ensure durability. The camera and DIN 18040 display module feature a black glass cover. Easy and phased installationThe system can be installed in phases, in parallel to the progress of building work. In this way, it is possible to initially install only the lower part of a surface-mounted housing during construction of the shell; cables and modules can then be added when

Illustrations are similar and may deviate from originals.
Prices valid for United Kingdom with prices valid 01/26.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

they are needed.Individual inscription optionsCall button modules and info modules can be labelled individually via the Gira inscription service.

Features

- Easy-to-use, vandal-proof, and scratch-resistant call buttons.
- Function changes, e.g from 2-gang to 4-gang, can be easily implemented by replacing the buttons.
- Various inscription options possible.

Technical data

Power supply	
- System:	via flat ribbon cable, 10-pole
Power consumption	
- Maximum:	160 mW
- Standby mode:	14 mW
Connections	
- System:	2 x connector strip
Ambient temperature:	-25 °C to +70 °C
Protection class:	IP54

Notes

- Professional inscription by the Gira inscription servicewww.beschriftung.gira.de.
