


Analogue actuator, 4-gang for KNX



Spezifikation	Bestell-Nr.	VE	PS	EAN
 DRA	1022 00	1		4010337010708

Merkmale

- Analogue actuator, 4-gang DRA with integrated bus coupler converts KNX telegrams (1-byte and 2-byte) into analogue output signals.
- These analogue output signals enable heating, air conditioning and ventilation actuators to adapt their initial parameters based on bus information, and to participate in control processes.
- Voltage outputs with short-circuit protection.
- The initial state is indicated by the status LED.
- The initial parameters can be restrained.
- Switch off outputs not required.
- The four outputs are parameterised to voltage or current signals by the software.

Technische Daten

KNX medium:	TP256
Number of outputs:	4
Rated voltage:	AC 24 V
Connections	
- KNX:	Connection and junction terminal
- Power supply:	Screw terminals
- Outputs:	Screw terminals
Current signals at the output	
- 0 to 20 mA:	Load \leq 500 Ω
- 4 to 20 mA:	Load \leq 500 Ω
Voltage signals at the output	
- 0 to 1 V:	Load \geq 1 k Ω
- 0 to 10 V:	Load \geq 1 k Ω
Connection cross section:	Max. 4 mm ²
Ambient temperature:	-5 °C to +45 °C

Hinweise

- Only while stocks last.

Lieferumfang

- Connection and junction terminal for KNX included with delivery.

Abmessungen

Teilungseinheiten (TE): 4
