© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

DCS camera gateway



Specification	Order No.	Packing unit	PS	EAN
	1201 00	1		4010337100034

Features

- The DCS camera gateway integrates a standard analogue camera into the Gira door communication system.
- The camera can be assigned to a door station. In this case, the external camera switches on automatically when the call button is pressed.

The combination housing of the DCS-camera-gateway makes three installation types possible:

- Surface-mounted (in a standard junction box).
- Flush-mounted (in a device box).
- as a DRA device (using the DRA adapter enclosed)

Technical data

Connections	
- 2-wire bus OUT:	2 x screw terminal
- 2-wire bus IN:	2 x screw terminal
- Video In:	2 x screw terminal
- Push terminals:	2 x screw terminal
- Relay (2-way switch):	3 x screw terminal
Ambient temperature:	-25 °C to +70 °C
Video signal:	FBAS 1 Vss, PAL standard
Dimensions	
- DCS camera gateway:	W 36 x H 52 x D 27 mm

Notes

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

- With several external cameras, a DCS-camera-gateway and a separate power supply is required for each external camera.
- Up to ten DCS-camera-gateways can be used in a system, although the video signal may only run through a maximum of three DCS-camera-gateways.
- The external camera is connected with screw terminals.

Scope of supply

- An adapter is included for cameras with a BNC connection.

Illustrations are similar and may deviate from originals.