


Built-in speaker



Spezifikation	Bestell-Nr.	VE	PS	EAN
	1258 00	1		4010337258001

Merkmale

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, allowing easy installation and expandability.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Built-in loudspeaker for mounting in letterbox systems, voice compartments, door-side installations or front panels.
- Up to eight mechanical bell buttons can be connected to the screw terminals provided.
- Signal transmission and power supply of loudspeaker via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Compact size.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Alternating current polling of the bell button connections to prevent oxidation on the button contacts.
- Securing of connection terminals against incorrect connection.
- Up to eight mechanical bell buttons can be connected.
- Colour camera for door station can be connected.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Voice volume adjustable.
- One-man commissioning with simple commissioning procedure.
- Acknowledgement tone when call button is pressed.

Technische Daten

Connecting the connection cable:	2 x connector strip
Protection class:	IP44
Power supply:	DC 26 V ± 2 V (by 2-wire bus)
Connections	
- 2-wire bus:	2 x screw terminal
- Additional power supply:	2 x screw terminal
- Mech. Bell button:	8 x screw terminal
- Common earth of bell buttons:	1 x screw terminal
- Connection cable:	2 x connector strip
- Video:	1 x connector strip

Ambient temperature: -25 °C to +70 °C

Dimensions
- W x H x D: 101 x 67 x 27 mm

Hinweise

- This component enables door communication systems with up to 140 audio devices to be set up (e.g. 1 x built-in speaker, 11 x add-on modules for built-in speakers, 136 x surface-mounted home stations).
 - The video control device is required if the system is expanded with a colour camera.
 - Protection type IP44 only in combination with a suitable front or when installed.
-