



## Gira energy profile with light element height 769 mm 3 SCHUKO socket outlets



Spezifikation	Bestell-Nr.	VE	PS	EAN
 anthracite	1342 28	1		4010337342281
 colour aluminium	1342 26	1		4010337342267

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

### Merkmale

- Gira energy profile with light element and three SCHUKO socket outlets.
- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation lighting.
- The two upper socket outlets are rotated by 30°.
- A 5-pole screw terminal for rigid and flexible conductors up to 4 mm<sup>2</sup> is used for connection.

### Technische Daten

Protection type (device cover closed):	IP44
Dimensions	
- Base:	W 229 x H 10 x D 155 mm
- Profile:	W 142 x H 769 x D 75 mm

## Hinweise

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
  - For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
  - Recommendation: Mount an RCCB prior to the device.
  - Single wall plug mounting.
  - Suitable for E27 light sources with energy efficiency classes A++ to E.
- 

## Lieferumfang

- Three SCHUKO socket outlets are included with delivery.
  - The mounting materials are included with delivery.
  - Light sources are not included with delivery.
-