© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Shutter actuator, 4-gang AC 230 V with manual actuation for KNX**



| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
|  DRA | 2160 00 | 1 | | 4010337101352 |

**Features**

- Shutter actuator with manual activation and status display for each output.
- With integrated bus coupler.
- For controlling electrically operated shutters for mains voltage AC 230 V (4-channel).
- Connection of various external conductors.
- Independent control of the four shutter outputs.
- Shutter position can be directly controlled.
- Behaviour after bus voltage failure and recovery can be set.
- Feedback of position. Active or passive (object can be read out) cyclical feedback functions.
- Assignments of up to five different safety functions (three wind alarms, one rain alarm, one frost alarm) or optionally with cyclical monitoring.
- Building site operation: Outputs can be operated manually without bus voltage with operating voltage only.

**Technical data**

| | |
|---|---|
| KNX medium: | TP256 |
| Rated voltage: | AC 230 V, 50/60 Hz |
| AC switching voltage: | AC 230 V, 50/60 Hz |
| Breaking capacity 230 V AC: | 6 A/AC1 |
| Connections | |
| - KNX: | Connection and junction terminal |
| - Load: | Load via screw terminals |
| Connection cross section: | Max. 4 mm² |

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Notes**

- VDE approval in accordance with EN 60669-1, EN 60669-2-1.
- Installation on DIN top-hat rail.

---

**Scope of supply**

- Connection and junction terminal for KNX included with delivery.

---

**Dimensions**

| | |
|---|---|
| Modular width (MW): | 4 |

---