


System 3000 universal LED power booster DRA



Spezifikation	Bestell-Nr.	VE	PS	EAN
 DRA	2383 00	1		4010337031383

Merkmale

- Switching and dimming light bulbs, HV halogen lamps, electronic transformers for halogen, inductive transformers for halogen, HV LED or compact fluorescent lamps.
- Operation is via upstream dimmer.
- The connected loads are supplied via a common load line.
- Electronic excess-temperature protection.

Technische Daten

Rated voltage: AC 230 V, 50/60 Hz

Standby: 0.3 W

Connected load at 45 °C

- HV LED lamps (leading edge): 50 to 100 W
- HV LED lamps (trailing edge): 200 W
- Light bulbs: 210 to 420 W
- HV halogen lamps: 210 to 420 W
- Tronic transformers: 210 to 420 W
- Wound electronic transformer: 210 to 420 VA

Cable length

- Load: Max. 100 m

Ambient temperature: -5 °C to +45 °C

Hinweise

- If the ambient temperature is higher than 45 °C, the connected load must be reduced.
 - Maximum load and number of power boosters depend on dimmer. Refer to the technical appendix or operating instructions for a reference list.
-