

## System 3000 universal LED rotary dimming insert Standard



Spezifikation	Bestell-Nr.	VE	PS	EAN
	2450 00	1/5		4010337031406

### Merkmale

- Switching and dimming light bulbs, HV halogen lamps, electronic transformers for halogen or LED lights, dimmable inductive transformers for halogen or LED lights, HV LED or compact fluorescent lamps.
- Automatic setting of dimming principle according to load (leading or trailing edge).
- Switch-on function that preserves the life of the lamp.
- Switch-on brightness can be saved permanently.
- Switch on with the last brightness set, or a saved switch-on brightness.
- Minimum brightness can be set.
- Electronic short-circuit protection.
- Electronic excess-temperature protection.
- Operation with or without a neutral conductor connection.
- Maximum brightness can be set (from index I04).

### Technische Daten

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.35 W
Connected load at 25 °C	
- HV LED lamps (leading edge):	typically 3 to 60 W
- HV LED lamps (trailing edge):	typically 3 to 120 W
- Compact fluorescent lamp:	typically 3 to 60 W
- Light bulbs:	20 to 210 W
- HV halogen lamps:	20 to 210 W
- Tronic transformers:	20 to 210 W
- electronic transformer with NV-LED:	typically 20 to 60 W
- Wound electronic transformer:	20 to 210 VA
- Wound transformer with NV-LED:	typically 20 to 60 VA
Cable length	
- Load:	Max. 100 m
Installation:	in device box pursuant to DIN 49073
Installation depth:	24 mm

Ambient temperature: -5 °C to +45 °C

---

## Hinweise

- In principle, it is possible to operate the dimmer without connecting the neutral conductor, but some LED and CFLi light sources make the neutral conductor connection necessary to avoid flickering.
  - Operation without a neutral conductor increases the minimum load for light bulbs, HV halogen lamps, Tronic transformers and wound transformers to 50 W.
  - Electronic transformers and ballast devices for LED lamps can be operated with the dimming procedure specified by the manufacturer.
  - If the ambient temperature is higher than 25 °C, the connected load must be reduced.
-