© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**Gira Keyless In Keypad TX_44**




| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
|  pure white | 2605 66 | 1 | | 4010337051428 |
|  anthracite (lacquered) | 2605 67 | 1 | | 4010337051435 |
|  colour aluminium (lacquered) | 2605 65 | 1 | | 4010337051411 |

**Features**

- Keypad as an access control system with a capacitive and therefore wear-free button field.
- No recognisable wear on frequently used number combinations.
- Stand-alone device or in combination with the Gira door communication system as a door call system for buildings with several residential units.
- Special button "C": Deleting an incorrect entry.
- Special button "Key": Direct door opening when the correct code has been entered.
- Special button "Bell": Specific selection of home stations in large facilities.
- Special button "F": Switching functions with switching actuators from the Gira door communication system.
- Homogeneous blue LED lighting of the numbers and special characters at night.
- Master PIN number provided on included sealed safety card if Administrator PIN number is lost.
- The keypad can manage up to 255 codes.
- Up to 32-digit codes are possible.
- Audible feedback when buttons are touched.
- 3-colour LED status display when programming and during operation.
- Warning tone in case of unauthorised removal of the keypad top unit for tamper detection. Tampering circuit with switching actuator in the Gira door communication system.
- The two integrated 2-way momentary contact relays can be assigned two different codes, e.g. code 1: open door, code 2: switching outside light.

Inputs and outputs

- Connector strip connection cable for Gira door communication system.

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Technical data**

| | |
|---|---|
| Power supply | |
| - Additional power supply: | DC 24 V ±5% |
| - from the door communicationsystem: | DC 26 V ± 2 V |
| Relay | |
| - Quantity: | 2 |
| - Contact: | 1 zero-voltage 2-way momentary contact |
| - Load capacity: | AC/DC 24 V / 1.6 A |
| Connections | |
| - Connection cable for door communication: | 1 x connector strip |
| - Relay: | 3 screw terminals each |
| - Additional power supply: | 2 x screw terminal |
| Resistance to EMD: | up to 16 kV |
| Installation depth: | 35 mm |
| Ambient temperature: | -20 °C to +70 °C |

---

**Notes**

- Keyless In devices can be connected to the Gira HomeServer using the DCS-IP gateway. This enables intelligent links. In this way, e.g. temporary or one-time access authorisation can be easily granted. All data including access authorisations can be managed centrally and flexibly using the Gira HomeServer.
- The Gira AppShop is the marketplace for interesting solutions and applications in intelligent building technology. There are now more than 200 apps available, including application descriptions, plug-ins, function templates, logic nodes and sample projects. Discover applications for the Gira Keyless In keypad now.www.appshop.gira.de/en.

---