© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

eNet Radio switching actuator or momentary-contact actuator, 2-gang Mini



Specification	Order No.	Packing unit	PS	EAN
	5425 00	1/5		4010337774228

Features

- The eNet wireless switching or momentary-contact actuator enables the switching of lighting and motors.
- Operating modes: Switching actuator or momentary-contact actuator together for both outputs.
- Status feedback to eNet radio transmitter.
- Scene operation.
- Operating mode buttons: Relay contact stays closed as long as telegrams are being received (max. 60 seconds).

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.5 W
Ambient temperature:	-25 °C to +70 °C
Breaking capacity 230 V AC:	16 A/AC1
Connected load	
- Light bulbs:	2300 W
- HV halogen lamps:	2000 W
- Wound electronic transformer:	1000 VA
- Tronic transformer:	1500 W
- Fluorescent lamps, uncompensated:	920 VA
- LED lights:	typically 500 W
- Compact fluorescent lamp:	typically 500 W
- Motors:	450 W
- Capacitive load:	690 VA (560 µF)
Connection cross section:	Max. 4 mm²
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m
Dimensions:	Ø 53,0 H 28,0 mm

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

Notes

- Mounting in device box, surface-mounted housing or in installation adapter.

Illustrations are similar and may deviate from originals.