


eNet Radio switching actuator or momentary-contact actuator, 1-gang



Spezifikation	Bestell-Nr.	VE	PS	EAN
 DRA	5433 00	1		4010337774273

Merkmale

- The eNet wireless switching or momentary-contact actuator receives telegrams for switching lighting from the eNet wireless receiver module or eNet server via a data line.
- Operating modes: Switching actuator or momentary-contact actuator.
- Status feedback to eNet radio transmitter.
- Scene operation.
- Operating mode buttons: Relay contact stays closed as long as telegrams are being received (max. 60 seconds).

Can be set with eNet server:

- Flashing function.
- Delay time.
- Switch-on/off delay.
- Switch-off pre-warning.
- Minimum switching repeat time.
- Permanent-on, permanent-off.

Technische Daten

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.2 W
Ambient temperature:	-5 °C to +45 °C
Breaking capacity 230 V AC:	16 A/AC1
Connected load	
- Light bulbs:	2300 W
- HV halogen lamps:	2000 W
- Wound electronic transformer:	1000 VA
- Tronic transformer:	1500 W
- Fluorescent lamps, uncompensated:	920 VA
- LED lights:	typically 500 W
- Compact fluorescent lamp:	typically 500 W
- Capacitive load:	690 VA (560 µF)

Connection cross section: Max. 4 mm²

Length of the data line: Max. 3 m

Hinweise

- An eNet wireless receiver module or an eNet server is required to operate this DIN rail adapter.

Abmessungen

Teilungseinheiten (TE): 2
