

## BNC insert, 2-gang Crimp connection



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	5630 03	1/5		4010337460251
 black matt	5630 10	1/5		4010337460268

### Technische Daten

Wave impedance:	50 $\Omega$
Installation depth:	25 mm

### Hinweise

- Not suitable for mounting frames with hinged covers.
- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes  
Flush-mounted installation: Kaiser order no.: 1068-02  
Cavity mounting: Kaiser order no.: 9062-94  
Concrete installation: Kaiser order no.: 1268-40